
100/200/300/400

USB OUTPUT INTERFACE




- The cable without software, push the black button or footswitch, the data can be transferred into Excel, Word directly.
- The cable with software, the data can be transferred into the software at a set interval time automatically.






Software



		Auto Start	nual	Ma	Save		Clear
0.000 mm	Δ		n	ollection	Data c		
U. UUU IIII I	υ.	ime	Ti	Result	Error	Value	No
		3 10:27:13	2024-08-23	NG	-1.000	0.000	000001
		3 10:27:14	2024-08-23	NG	-0.100	0,900	000002
		3 10:27:15		OK	2,470	3.470	000003
Zero	nect	3 10:27:16 Discom		OK	5.150	6.150	000004
SC	ASC	3 10:27:17		NG	7.730	8,730	000005
		3 10:27:18		NG	11.370	12,370	000006
		3 10+27+19		NG	14.310	15, 310	000007
CS	e statistics	3 10:27:20 Real-tim		NG	18,330	19.330	800000
		3 10+27+21		NG	20, 250	21,250	000009
Num 17 NG+ 6	8.82294 Num	3 10:27:22 AVG		NG	22,600	23,600	000010
	-	3 10:27:27		OK	5.810	6.810	000011
OK 9 NG- 2	23.6 OK			OK	5,450	6,450	000012
on jo no- ja	123.0	3 10:27:29	2024-08-23	OK	5,100	6.100	000013
		3 10:27:30		OK	4,680	5,680	000014
	0		2024-08-23	OK	4,130	5,130	000015
			2024-08-23	OK	3.510	4.510	000016
		3 10:27:32	2024-08-23	OK	3,200	4,200	000017
	rs	Paranete					
Beep off - Auto 200 Sampling Ms	1 Beep	STD					
Unit mm - period ms	6 Unit	USL					
	1	LSL					
Parameters	P						
Internal debug: E 0 M							

Code	Software	Plug to product	Products
100-03	Without		for digital calipers with following electronics
100-04	With		
100-03L	Without	Ç	for digital height gage with following electronics
100-04L	With	8mm	
100-11	Without	THE REAL PROPERTY AND A DESCRIPTION OF A	for digital calipers with following electronics
100-12	With		(81)
100-15	Without		for digital calipers and height gage with following electronics
100-17	Without		for digital calipers with following electronics

*Confirm the electronics output port type when placing orders



Code	Name
400-01	foot switcht

CABLE